

Connecting elements
H1,5/12S R

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H1,5/12S R
Order No.	9025690000
Version	Wire-end ferrule, insulated, 8 mm, 6 mm, red
GTIN (EAN)	4008190059439
Qty.	500 pc(s).
Packaging	loose

Data sheet

Connecting elements H1,5/12S R

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	12 mm	Width (inches)	0.472 inch
Net weight	0.097 g		

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	3.9 mm	Colour code	Weidmüller
Conductor cross-section	1.5 mm ²	Contact surface diameter (D1)	1.7 mm
Contact surface length (L2)	6 mm	L1 in mm	12 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	8 mm	Wire connection cross section AWG, max.	AWG 16

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	WSCAD, EPLAN
Engineering Data	STEP

Data sheet

**Connecting elements
H1,5/12S R**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Similar to illustration

