

## Connecting elements H0,75/14 W SV

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H0,75/14 W SV
Order No.	<a href="#">9026070000</a>
Version	Wire-end ferrule, insulated, 10 mm, 8 mm, white
GTIN (EAN)	4008190187163
Qty.	500 pc(s).
Packaging	Multipack bag

**Connecting elements**  
**H0,75/14 W SV**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	14 mm	Width (inches)	0.551 inch
Net weight	0.1 g		

**Technical data**

Version	insulated
---------	-----------

**Wire-end ferrules**

Collar diameter (D2)	2.8 mm	Colour code	Weidmüller
Conductor cross-section	0.75 mm <sup>2</sup>	Contact surface diameter (D1)	1.2 mm
Contact surface length (L2)	8 mm	L1 in mm	14 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	10 mm	Wire connection cross section AWG, max.	AWG 18

**Classifications**

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**Connecting elements  
H0,75/14 W SV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Similar to illustration**

---

