

**Connecting elements**  
**H70,0/37 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

**General ordering data**

|            |   |
|------------|---|
| Type       | H70,0/37 GE                                       |
| Order No.  | <a href="#">9028200000</a>                        |
| Version    | Wire-end ferrule, insulated, 26 mm, 21 mm, yellow |
| GTIN (EAN) | 4008190891572                                     |
| Qty.       | 25 pc(s).   |
| Packaging  | loose   |

## Data sheet

### Connecting elements H70,0/37 GE

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |       |                |            |
|------------|-------|----------------|------------|
| Width      | 40 mm | Width (inches) | 1.575 inch |
| Net weight | 3.9 g |                |            |

### Technical data

|         |           |
|---------|-----------|
| Version | insulated |
|---------|-----------|

### Wire-end ferrules

|                             |                    |   |            |
|-----------------------------|--------------------|---|------------|
| Collar diameter (D2)        | 16 mm              | Colour code                             | Weidmüller |
| Conductor cross-section     | 70 mm <sup>2</sup> | Contact surface diameter (D1)           | 12.7 mm    |
| Contact surface length (L2) | 21 mm              | L1 in mm                                | 37 mm      |
| Metal sleeve thickness (S1) | 0.35 mm            | Plastic collar thickness (S2)           | 0.6 mm     |
| Stripping length            | 26 mm              | Wire connection cross section AWG, max. | AWG 2/0    |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000005    | ETIM 4.0   | EC000005    |
| ETIM 5.0   | EC000005    | ETIM 6.0   | EC000005    |
| UNSPSC     | 31-16-31-02 | eClass 5.1 | 27-40-02-01 |
| eClass 6.2 | 27-40-02-01 | eClass 7.1 | 27-40-02-01 |
| eClass 8.1 | 27-40-02-01 | eClass 9.0 | 27-40-02-01 |
| eClass 9.1 | 27-40-02-01 |            |             |

### Approvals

Approvals



ROHS Conform

### Downloads

|                    |  |
|--------------------|--|
| Brochure/Catalogue | <a href="#">CAT 6 TOOLS 15/16 EN</a>     |
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a> |
| Engineering Data   | <a href="#">STEP</a>                     |