
Connecting elements
H95,0/44 R

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H95,0/44 R
Order No.	9028210000
Version	Wire-end ferrule, insulated, 31 mm, 25 mm, red
GTIN (EAN)	4008190891589
Qty.	25 pc(s).
Packaging	loose

Connecting elements
H95,0/44 R

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	44 mm	Width (inches)	1.732 inch
Net weight	5.2 g		

Technical data

Version	insulated

Wire-end ferrules

Collar diameter (D2)	18 mm	Colour code	Weidmüller
Conductor cross-section	95 mm²	Contact surface diameter (D1)	14.7 mm
Contact surface length (L2)	25 mm	L1 in mm	44 mm
Metal sleeve thickness (S1)	0.35 mm	Plastic collar thickness (S2)	0.6 mm
Stripping length	31 mm	Wire connection cross section AWG, max.	AWG 3/0

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals	C SA US
ROHS	Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP