

Connecting elements
H120,0/50 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H120,0/50 BL
Order No.	9028220000
Version	Wire-end ferrule, insulated, 36 mm, 30 mm, blue
GTIN (EAN)	4008190891596
Qty.	25 pc(s).
Packaging	loose

Connecting elements

H120,0/50 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	50 mm	Width (inches)	1.969 inch
Net weight	9.08 g		

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	21 mm	Colour code	Weidmüller
Conductor cross-section	120 mm ²	Contact surface diameter (D1)	16.5 mm
Contact surface length (L2)	30 mm	L1 in mm	50 mm
Metal sleeve thickness (S1)	0.5 mm	Plastic collar thickness (S2)	0.7 mm
Stripping length	36 mm	Wire connection cross section AWG, max.	AWG 4/0

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP