

Connecting elements
H150,0/54 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H150,0/54 GE
Order No.	9028230000
Version	Wire-end ferrule, insulated, 38 mm, 32 mm, yellow
GTIN (EAN)	4008190891602
Qty.	25 pc(s).
Packaging	loose

Connecting elements

H150,0/54 GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	54 mm	Width (inches)	2.126 inch
Net weight	10.8 g		

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	23.5 mm	Colour code	Weidmüller
Conductor cross-section	150 mm ²	Contact surface diameter (D1)	18.5 mm
Contact surface length (L2)	32 mm	L1 in mm	54 mm
Metal sleeve thickness (S1)	0.5 mm	Plastic collar thickness (S2)	0.75 mm
Stripping length	38 mm	Wire connection cross section AWG, max.	AWG 300 MCM

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP