

## Connecting elements H2,5/16DS BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

Type	H2,5/16DS BL
Order No.	<a href="#">9036220000</a>
Version	Wire-end ferrule, insulated, 13 mm, 10 mm, blue
GTIN (EAN)	4032248068012
Qty.	500 pc(s).
Packaging	loose

## Data sheet

### Connecting elements H2,5/16DS BL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	16 mm	Width (inches)	0.63 inch
Net weight	0.16 g		

### Technical data

Version	insulated
---------	-----------

### Wire-end ferrules

Collar diameter (D2)	4.2 mm	Colour code	Weidmüller
Conductor cross-section	2.5 mm <sup>2</sup>	Contact surface diameter (D1)	2.2 mm
Contact surface length (L2)	10 mm	L1 in mm	16 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	13 mm	Wire connection cross section AWG, max.	AWG 14

### Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

### Approvals

Approvals



ROHS Conform

### Downloads

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**Connecting elements  
H2,5/16DS BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Similar to illustration**

---

---

---

