


## Connecting elements H1,5/20D ZH SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

### General ordering data

Type	H1,5/20D ZH SW
Order No.	<a href="#">9037480000</a>
Version	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, black
GTIN (EAN)	4008190493059
Qty.	500 pc(s).
Packaging	loose

**Connecting elements**  
**H1,5/20D ZH SW**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	20 mm	Width (inches)	0.787 inch
Net weight	0.178 g		

**Technical data**

Version	Twin wire-end ferrule
---------	-----------------------

**Wire-end ferrules**

Collar height (A)	6.5 mm	Collar width (B)	3.6 mm
Colour code	DIN	Conductor cross-section	1.5 mm <sup>2</sup>
Contact surface diameter (D1)	2.2 mm	Contact surface length (L2)	12 mm
L1 in mm	20 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.3 mm	Stripping length	15 mm
Wire connection cross section AWG, max.	AWG 16		

**Classifications**

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**Connecting elements  
H1,5/20D ZH SW**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Similar to illustration**

