

**Connecting elements  
H10,0/24D ZH R**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

**General ordering data**

Type	H10,0/24D ZH R
Order No.	<a href="#">9037570000</a>
Version	Wire-end ferrule, Twin wire-end ferrule, 17 mm, 12 mm, red
GTIN (EAN)	4008190493141
Qty.	100 pc(s).
Packaging	loose

**Connecting elements  
H10,0/24D ZH R**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	24 mm	Width (inches)	0.945 inch
Net weight	0.8 g		

**Technical data**

Version	Twin wire-end ferrule
---------	-----------------------

**Wire-end ferrules**

Collar height (A)	13.4 mm	Collar width (B)	7.6 mm
Colour code	DIN	Conductor cross-section	10 mm <sup>2</sup>
Contact surface diameter (D1)	5.8 mm	Contact surface length (L2)	12 mm
L1 in mm	24 mm	Metal sleeve thickness (S1)	0.2 mm
Plastic collar thickness (S2)	0.5 mm	Stripping length	17 mm
Wire connection cross section AWG, max.	AWG 8		

**Classifications**

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**Connecting elements  
H10,0/24D ZH R**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Similar to illustration**

---

