
Connecting elements
H16,0/38D ZH BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For the following wires: 2 x 16.0 mm² (2 x AWG 6)
- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H16,0/38D ZH BL
Order No.	9037600000
Version	Wire-end ferrule, Twin wire-end ferrule, 29 mm, 25 mm, blue
GTIN (EAN)	4008190493196
Qty.	50 pc(s).
Packaging	loose

Connecting elements
H16,0/38D ZH BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	38 mm	Width (inches)	1.496 inch
Net weight	1.86 g		

Technical data

Version	Twin wire-end ferrule

Wire-end ferrules

Collar height (A)	17.2 mm	Collar width (B)	9.5 mm
Colour code	DIN	Conductor cross-section	16 mm²
Contact surface diameter (D1)	8.3 mm	Contact surface length (L2)	25 mm
L1 in mm	38 mm	Metal sleeve thickness (S1)	0.3 mm
Plastic collar thickness (S2)	0.6 mm	Stripping length	29 mm
Wire connection cross section AWG, max.	AWG 6		

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals	
ROHS	Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP