

Connecting elements
H0,75/14T ZH HBL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For the following conductors: 2 No. 0.75 mm² (2 No. AWG 18)

- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H0,75/14T ZH HBL
Order No.	9037610000
Version	Wire-end ferrule, Twin wire-end ferrule, 11 mm, 8 mm, Light Blue
GTIN (EAN)	4008190493233
Qty.	500 pc(s).
Packaging	loose

Connecting elements
H0,75/14T ZH HBL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	14 mm	Width (inches)	0.551 inch
Net weight	0.132 g		

Technical data

Version	Twin wire-end ferrule
---------	-----------------------

Wire-end ferrules

Collar height (A)	5.5 mm	Collar width (B)	3 mm
Colour code	Telemecanique	Conductor cross-section	0.75 mm ²
Contact surface diameter (D1)	1.7 mm	Contact surface length (L2)	8 mm
L1 in mm	14 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.3 mm	Stripping length	11 mm
Wire connection cross section AWG, max.	AWG 18		

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

Data sheet

Connecting elements
H0,75/14T ZH HBL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Similar to illustration

