

Connecting elements
H4,0/22T ZH OR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- supplied loose in poly-bag
- DIN colour code
- other colour code

General ordering data

Type	H4,0/22T ZH OR
Order No.	9037670000
Version	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, orange
GTIN (EAN)	4008190493431
Qty.	100 pc(s).
Packaging	loose

**Connecting elements
H4,0/22T ZH OR**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	22 mm	Width (inches)	0.866 inch
Net weight	0.48 g		

Technical data

Version	Twin wire-end ferrule
---------	-----------------------

Wire-end ferrules

Collar height (A)	9 mm	Collar width (B)	5.2 mm
Colour code	Telemecanique	Conductor cross-section	4 mm ²
Contact surface diameter (D1)	3.5 mm	Contact surface length (L2)	12 mm
L1 in mm	22 mm	Metal sleeve thickness (S1)	0.2 mm
Plastic collar thickness (S2)	0.5 mm	Stripping length	15 mm
Wire connection cross section AWG, max.	AWG 12		

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

Data sheet

**Connecting elements
H4,0/22T ZH OR**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Similar to illustration

