

## cable lug, terminal end LIS 6M10 V

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



### Insulated forked-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

### General ordering data

|            |  |
|------------|--|
| Type       | LIS 6M10 V   |
| Order No.  | <a href="#">9200450000</a>   |
| Version    | cable lug, terminal end, Insulated cable connector, 4 mm <sup>2</sup> - 6 mm <sup>2</sup> , yellow |
| GTIN (EAN) | 4032248410293  |
| Qty.       | 100 pc(s).   |

**Data sheet**

**cable lug, terminal end  
LIS 6M10 V**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

|            |         |                |            |
|------------|---------|----------------|------------|
| Width      | 36.7 mm | Width (inches) | 1.445 inch |
| Depth      | 8 mm    | Depth (inches) | 0.315 inch |
| Net weight | 3.17 g  |                |            |

**Connectors**

|                               |                   |                               |                   |
|-------------------------------|-------------------|-------------------------------|-------------------|
| Conductor cross-section, max. | 6 mm <sup>2</sup> | Conductor cross-section, min. | 4 mm <sup>2</sup> |
| Connection density (S1)       | 1 mm              | Dimension                     | M 10              |
| Dimension (bolt)              | M 10              | Identification colour         | yellow            |
| Inside diameter (d1)          | 10.5 mm           | Insulation                    | Available         |
| Material/plastic              | PVC               | Outside diameter (d)          | 18 mm             |
| Plastic collar diameter (D)   | 6.4 mm            | Plastic collar length (b)     | 13.15 mm          |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000494    | ETIM 4.0   | EC000494    |
| ETIM 5.0   | EC001059    | ETIM 6.0   | EC001059    |
| UNSPSC     | 41-11-36-37 | eClass 5.1 | 27-20-03-08 |
| eClass 6.2 | 27-40-02-04 | eClass 7.1 | 27-40-02-04 |
| eClass 8.1 | 27-40-02-12 | eClass 9.0 | 27-40-02-92 |
| eClass 9.1 | 27-40-02-12 |            |             |

**Approvals**

Approvals



ROHS Conform

**Downloads**

|                    |                                      |
|--------------------|--------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 6 TOOLS 15/16 EN</a> |
| Engineering Data   | <a href="#">EPLAN</a>                |

**Data sheet**

**cable lug, terminal end  
LIS 6M10 V**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

