

Group markers
WAD 20 GE WSD**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	WAD 20 GE WSD
Order No.	9512260000
GTIN (EAN)	4008 190403942
Qty.	10 pc(s).

Data sheet

Group markers WAD 20 GE WSD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	18 mm	Width (inches)	0.709 inch
Height	48.5 mm	Height (inches)	1.909 inch
Depth	13.43 mm	Depth (inches)	0.529 inch
Net weight	2.323 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	PA 66	Colour	yellow
UL 94 flammability rating	V-2		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Snap-on		

Dimensions

Pitch in mm (P)	18 mm
-----------------	-------

Classifications

ETIM 3.0	EC000897	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000761
UNSPSC	30-21-18-11	eClass 5.1	27-14-11-45
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-37
eClass 9.1	27-14-11-37		

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	32165_WAD_20_GE_DXF.dxf STEP