




Artikel-Nr.: 0204047

Bez.: Mini-DIN-Einbaubuchse, 4-pol.



PCB LAYOUT
BOTTOM VIEW

SPECIFICATION:

1. CURRENT CARRYING CAPACITY : 1) AC : 100V 1A MAX .
2) DC : 12V 2A MAX .
2. CONTACT RESISTANCE : 30m OHM MAX .
3. INSULATION RESISTANCE : 50M OHM MIN . AT DC 250V .
4. VOLTAGE WITHSTANCE : AC 250V 1 MINUTE .
5. INSERTION FORCE: 1.0KG - 4.5KG
WITHDRAWAL FORCE: 0.8KG - 3.0KG

ARRANGEMENT OF CONTACTS				
NO OF CONTACTS	3	4	6	8
HOLE LAYOUT				

4.	CONTACTOR	8	PBR 0.2t	SILVER PLATED	
3.	EARTH TERMINAL	1	BSR 0.4t	TIN	
2.	COVER	1	P.B.T		UL94V-0
1.	BODY	1	P.B.T		UL94V-0
P/N	PART NAME	Q'TY	MATERIAL	PLATING	REMARKS

www.bkl-electronic.de

Technische Änderungen vorbehalten. Ausführungen können variieren. Sollten Sie ein Muster benötigen kontaktieren Sie uns bitte.

BKL-ELECTRONIC Kreimendahl GmbH • Märkenstück 14 • 58509 Lüdenscheid
Tel: +49 (0)2351-3621-0 • Fax: +49 (0)2351-3621-29 • info@bkl-electronic.de

