


RS 90 PF RS 90 OR 2000MM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Flexible - More flexible - Profilform

Modular housings in profile form - the flexible modular system comprising coloured and transparent plastic profiles and carrier modules

The combination of standard pitches mounted side by side in any arrangement and metre goods cut accurate to the millimetre creates the perfect balance between flexibility and economic efficiency:

- Pitch profiles with standard widths ranging from 5mm to 45mm allow the mounting of all standard PCB formats.
- Variable heights ensure maximum component density, even with larger electronics components.
- The different installation variations mean that mounting the enclosure directly is as easy as clipping components onto the terminal rail
- Solid hoods protect the module reliably from external influences

The recipe for success: variable profile + modular form components = flexible enclosure concept that offers a large surface area for the PCBs.

The modular concept is designed for modules with high space requirements and suitable for small component quantities and different widths.

General ordering data

Type	PF RS 90 OR 2000MM
Order No.	4053240000
Version	Electronics housings, RS 90 orange, Extruded profile, Width: 84.4 mm
GTIN (EAN)	4032248005659
Qty.	2 m

RS 90 PF RS 90 OR 2000MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	2,000 mm	Length (inches)	78.74 inch
Width	84.4 mm	Width (inches)	3.323 inch
Height	15.7 mm	Height (inches)	0.618 inch
Net weight	315 g		

System characteristics

Version	Extruded profile	Number of PCBs per module	1
PCB thickness	1.6 mm	Tolerance for the PCB shape	±0.2
Cross-connection	No	Contact to terminal rail	No
Protection degree	IP20	Encapsulation option	No

Material data

Insulating material	PVC	Colour	orange
Colour chart (similar)	RAL 2000	CTI	≥ 600
UL 94 flammability rating	V-0	Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C	Max. relative humidity during storage	80 %
Operating temperature, min.	-50 °C	Operating temperature, max.	60 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	60 °C

Classifications

ETIM 5.0	EC002848	ETIM 6.0	EC002779
eClass 6.2	27-14-11-43	eClass 7.1	27-14-92-14
eClass 8.1	27-14-92-14	eClass 9.0	27-18-27-90
eClass 9.1	27-18-27-90		

Notes

Notes

Descriptive text technical data

Dimensions of the PCB:

Thickness: 1.6 (± 0.2) mm, width: 79.8 (+0.2) mm

Dimension of RS section = PCB length - 4.5 mm

Example:

PCB length 160 mm, RS section = 155.5 mm

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL ANALO.SIGN.CONV. EN MB DEVICE MANUF. EN CAT 2 PORTFOLIOGUIDE EN FL MACHINE SAFETY EN FL 72H SAMPLE SER EN PO OMNIMATE EN
--------------------	--

**RS 90
PF RS 90 OR 2000MM**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Drawings

