

**Device markers  
THM GEW FLAG 54/8 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers. Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

**General ordering data**

|            |                                                                             |
|------------|-----------------------------------------------------------------------------|
| Type       | THM GEW FLAG 54/8 WS                                                        |
| Order No.  | <a href="#">1107350000</a>                                                  |
| Version    | Device markers, Label, 54 x 8 mm, Vinyl-coated cotton fabric, Colour: White |
| GTIN (EAN) | 4032248882885                                                               |
| Qty.       | 1 pc(s).                                                                    |

## Device markers THM GEW FLAG 54/8 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |       |       |      |
|------------|-------|-------|------|
| Length     | 54 mm | Width | 8 mm |
| Net weight | 673 g |       |      |

### General data

|                                   |                            |                                              |           |
|-----------------------------------|----------------------------|----------------------------------------------|-----------|
| Adhesive                          | Natural rubber adhesive    | Colour                                       | White     |
| Material                          | Vinyl-coated cotton fabric | Material colour according to resistance code | 9         |
| Number per roll                   | 4,000                      | Number per sheet                             | 4,000     |
| Operating temperature range, max. | 80 °C                      | Operating temperature range, min.            | -29 °C    |
| Printing method                   | Thermotransfer             | Size of labelling field                      | 21x5.8 mm |
| UL 94 flammability rating         | HB                         | UL 969 flammability rating                   | No        |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001288    | UNSPSC     | 55-12-16-00 |
| eClass 5.1 | 27-14-91-29 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Downloads

|                                 |                                               |
|---------------------------------|-----------------------------------------------|
| M-Print® PRO configuration file | <a href="#">lab_thm_gew_flag_54_8_mcf.zip</a> |
|---------------------------------|-----------------------------------------------|