



OD 2940



Fruit Dryer

Colour / Material:

white

Output:

250 W

EAN-no.:

4008146294006



- dries fruits, vegetables and herbs
- 5 grates can be stacked up or used separately
- maximum temperature: approx. 85 °C (bottom) and 70 °C (top)
- plastic housing
- grates with two height adjustments
- motor with fan
- on-off switch with pilot light
- transparent lid
- diameter approx. 31 cm