

Product video



Contact grill PC-KG 1029

- Contact grill for double-sided, fat-free grilling
- Barbecue grill - 180° opening enables grilling on a large surface
- 2000 watt
- Stainless steel housing
- Central fat drainage channel and drip pan (tray removable for easy cleaning)
- Infinitely variable thermostat
- Short cooking times
- Non-stick grill plates with extra deep grooves for strong grill pattern and optimal fat runoff
- Grill plates removable for easy cleaning
- Large, heat-insulated handle with soft-touch insert
- On/off switch
- 2 indicator lights for power supply and heating
- Temperature "ready" display
- Large grilling surfaces: 23 x 29 cm
- Versatile, can be used for e.g. panini, steaks, fish, vegetables, eggs or desserts
- Power supply: 230-240 V, 50/60 Hz
- Power input: 2000 W

2000 watt

Stainless steel housing

Infinitely variable thermostat

Grill plates removable for easy cleaning



180° opening enables grilling on a large surface

Color: Stainless steel
 Article-No.: 501 029
 Article EAN-Code: 4 006 160 102 918
 Exportpack EAN-Code: 4 006 160 227 840
 PU: 2 pcs.
 Pallet:
 20"/40"/HQ Container: 916 / 1870 / 2114

Dimensions (approx. B x H x T) und wight
 Unit: 340 x 145 x 320 mm; 3,6 kg
 Box:

Delivery: begin of September 2012

ProfiCook
 Industriering Ost 40
 47906 Kempen/Germany
 Fon +49 (0) 21 52 / 89 98 0
 Fax +49 (0) 21 52 / 89 98 911
servicecenter@proficook.de
www.proficook.de