

KH1508A/KH1516A

8/16-port Cat 5 High-Density KVM Switch

ALTUSCN™
Enterprise KVM Solutions by ATEN

The KH1508A and KH1516A KVM switches are control units that allow IT administrators to access and control multiple computers from a single PS/2 or USB KVM console (keyboard, monitor, and mouse). Operators can take control of up to 8 (KH1508A), or 16 (KH1516A), computers. By daisy chaining up to 31 additional switches, as many as 512 computers can be controlled from the original KVM console.

These switches have been designed with unique and powerful features that enable administrators to manage their entire server room and data center devices easily and conveniently.

For example, the advanced Adapter ID feature stores the Adapter Cable's configuration information – such as its ID, port name, OS, keyboard language, etc. This feature allows administrators to relocate servers to different ports without having to reconfigure the adapters. Other advances found with these switches includes enhanced video quality – extending the distance to the servers to up to 50 m* at a resolution of 1280 x 1024.

A KH1508A or KH1516A installation provides one of the best, and most economical, solutions ATEN offers to the SMB market. There is no better way to save time, space, and money than with a KH1508A or KH1516A KVM switch.

*With KVM Adapter Cable KA7000 series, please see page 3 for details.

KH1508A



KH1516A



» FEATURES

- One KVM console control up to 8 or 16 directly connected computers
- Space-Saving RJ-45 connectors and Cat 5e/6 cabling
- By daisy chaining up to 31 additional KH1508A / KH1516A switches, as many as 512 computers can be controlled from the original KVM console
- Console conversion – any type of KVM console can control any type of computer; mixed combinations (PS/2&USB) supported on both the KVM console and computer sides
- Superior Video Quality- Supports the video resolutions up to 1600x1200@60Hz for up to 40 meters, and 1280x1024@75 Hz for up to 50 meters*
- Configure port access rights for users on a port - by - port basis
- Three port selection methods: Manual (via front panel pushbuttons), Hotkey, and multi-language OSD (On Screen Display)
- Multiplatform support – PC, Mac, Sun, and serial
- Multiple User Accounts -Supports up to 10 user and 1 administrator accounts
- Two-Level Password Security- Supports one administrator and ten user profiles. Strong password protection prevents unauthorized accessing to the installation
- Auto Scan mode enables continuous monitoring of user-selected computers
- Broadcast Mode sends commands from the console to all computers – allowing you to perform operations (such as software installation, upgrades, shutdowns, etc.), on them simultaneously
- Adapter ID
- Firmware Upgradeable

* With KVM Adapter Cable KA7000 series, please see page 3 for details.

» Benefits

Easy Operation

Three port selection methods: Manual (via front panel pushbuttons), Hotkey, and multi-language OSD (On Screen Display). Multi-language keyboard support includes US English, UK English, French, German, Swiss German, Hungarian, Italian, Japanese, Korean, Russian, Spanish, Swedish and Traditional Chinese.

Auto Scanning and Broadcast Mode

Auto scanning provides hands-free monitoring of selected devices at variable rates. Broadcast Mode sends commands from the console to all computers – allowing you to perform operations (such as software installation, upgrades, shutdowns, etc.), on them simultaneously.

Superior Video Quality

Supports the video resolutions up to 1600x1200@60Hz for up to 40 meters, and 1280x1024@75Hz for up to 50 meters with the new ATEN KVM Cable Adapter KA7000 series.

Multiple User Accounts Supports up to 10 user and 1 administrator accounts.

Space-Saving RJ-45 Connectors and Cat 5e/6 Cabling


This space-saving innovation means that the KH1508A /KH1516A can be conveniently installed in a 1U system rack, and the installation can take advantage of the internal network wiring built into most modern commercial buildings. Reduces cable clutter for a neat and tidy data center environment

Adapter Cables with ID

The KH1508A / KH1516A KVM series supports automatic ID recognition of the new ATEN KVM Cable Adapter KA7000 series. Using the new adapter cables with ID means it is not required to change cable configuration settings when moving cables from port to port. Device ID and attributes are stored in the adapter cables allowing you to hot-swap port connections without having to reconfigure attributes.

The following KVM Adapter Cables are required for use with the KH1508A / KH1516A:

| | | | | | | |
|------------|---|--|---|--|-------------------------------------|------------------------|
| | | | | | | |
| Type: | PS/2 | USB | PS/2 | USB | Sun Legacy | Serial |
| Interface: | 6-pin Mini-DIN Male 6-pin Mini-DIN Male HDB-15 Male | USB Type A Male HDB-15 Male | 6-pin Mini-DIN Male 6-pin Mini-DIN Male HDB-15 Male | USB Type A Male HDB-15 Male | 13W3 Male DIN 8 pin Male | RS-232 DB-9 Female |



» Specification

| Function | | KH1508A | KH1516A | |
|----------------------|------------------------|---|--|-------------------|
| Computer Connections | Direct | 8 | 16 | |
| | Max | 256 (via Daisy Chain) | 512 (via Daisy Chain) | |
| Port Selection | | OSD (On Screen Display); Hotkeys, Pushbuttons | | |
| Connectors | Console Ports | Keyboard | 1 x 6-pin Mini-DIN Female (Purple); 1 x USB Type A Female (White) | |
| | | Video | 1 x HDB-15 Female (Blue) | |
| | | Mouse | 1 x 6-pin Mini-DIN Female (Green); 1 x USB Type A Female (White) | |
| | KVM Ports | | 8 x RJ-45 Female | 16 x RJ-45 Female |
| | Daisy Chain | In | 1 x DB-25 Female (Black) | |
| | | Out | 1 x DB-25 Male (Black) | |
| | FW Upgrade | | 1 x RJ-11 Female (Black) | |
| Power | | 1 x 3-prong AC socket | | |
| Switches | Port Selection | | 8 x Pushbutton | 16 x Pushbutton |
| | KVM Reset | | 1 x Recessed pushbutton | |
| | FW Upgrade | | 1 x Slide | |
| | Power | | 1 x Rocker | |
| LEDs | Port | Online | 8 (Green) | 16 (Green) |
| | | Selected | 8 (Orange) | 16 (Orange) |
| | Power | | 1 (Blue) | |
| Station ID | | 1 x 2 Digit 7-segment (Orange) | | |
| Emulation | Keyboard | | PS/2; USB | |
| | Mouse | | PS/2; USB | |
| Scan Interval | | 1–255 seconds | | |
| Video | | 1600 x 1200 @ 60 Hz (40m); 1280 x 1024 @ 75 Hz (50m)*; | | |
| I/P Rating | | 100–240 VAC; 50/60 Hz; 1A | | |
| Power Consumption | | 120V/5.8W; 230V/6W | 120V/5.9W; 230V/6.1W | |
| Environment | Operating Temp. | | -0–40° C | |
| | Storage Temp. | | -20–60° C | |
| | Humidity | | 0–80% RH; Non-condensing | |
| Physical Properties | Housing | | Metal | |
| | Weight | | 2.74 kg | 2.77 kg |
| | Dimensions (L x W x H) | | 43.30 x 16.00 x 4.40 cm | |

* With KVM Adapter Cable KA7000 series, please see page 3 for details.

ATEN International Co., Ltd.

3F, No.125, Sec. 2, Datung Rd. Sijhih City, Taipei 221, Taiwan

Phone: +886-2-8692-6789 Fax: +886-2-8692-6767 www.aten.com E-mail: online@aten.com.tw



www.aten.com

