



TOOLCRAFT

Version Nr.: 1.0
Revision Nr.: 1.0
Datum: Jan. 2013

Technisches Datenblatt „PVC-Putzerband/Allzweck-Klebeband“ Technical data sheet „PVC Protective Tape“

Production Specification

Product Name	PVC Protective Tape
Part number	832450 ...
Application	Excellent for protection of metal surface during transportation & processing
Name of backing	Soft PVC (embossed)
Spec. of backing	0,13 mm (thickness) x 1330 mm (width) x 1000 m (length)
Color	blue, yellow, green, grey, orange, red, black, white
Type of adhesive	Rubber based
Coating thickness	15 – 17 μ

Theoretically speaking, the temperature resistant for a regular tape is between 0-36 degrees

<u>TEST ITEM</u>	<u>UNIT</u>	<u>SPECIFICATION</u>
Total thickness	mm	0,140 +/- 0,017
Adhesion	kg / 25 mm	0,350 \uparrow
Adhesion to backing	kg / 25 mm	NA
Initial tack	# of rolling ball	20 \uparrow
Holding power	minute	60 \uparrow
Tensile strength	kg / 25 mm	4 \uparrow
Elongation	%	100 \uparrow
Breakdown Volt.	Unit	NA
Volume resistivity	Ω -cm	NA

The Statements in this information sheet are based upon our knowledge and practical experience. This data is intended only as a source of information and is given without guarantee and does not constitute a warranty. Suggestion for use and final results on our best technical experiences but cannot be intended as our commitment or liability. The company reserves the right to modify or change the products at any time without notice. All information has to be intended as generic advise for the use of products. Users have to verify the suitability of each tape in actual application under specific conditions.