

eurolite®

Floorstands



Operating determinations



CAUTION!
The maximum load must never be exceeded!



CAUTION!
The load must always be installed in the centre of gravity!

When choosing the installation-spot, please make sure that the device is not exposed to extreme heat, moisture or dust. There should not be any cables lying around. Please make sure that the unit cannot be touched or bumped. You endanger your own and the safety of others!

Before rigging make sure that the installation area can hold a minimum point load of 10 times the device's weight.



CAUTION!
Install the spot via the screw.
Follow the instructions mentioned at the spot.
Make sure that the device is fixed properly!



The floorstand must be placed directly on the floor.

Technical specifications

	5900698A/B FS-1	5900698D/E FS-2	5900698G/H FS-3
Max. load WLL (2-fold):	20 kg	30 kg	50 kg
Max. load BGV C1 (4-fold):	10 kg	15 kg	25 kg
Mounting plate:	Thickness 2 mm	Thickness 3 mm	Thickness 4 mm
Bolt:	M10 x 25 mm	M10 x 25 mm	M10 x 25 mm
Dimensions (LxWxH):	215 x 215 x 45 mm	215 x 215 x 45 mm	300 x 300 x 50 mm
Weight:	0.15 kg	0.2 kg	0.5 kg