PRODUCT DATASHEET

NiMH Battery Charger (CH2PC4)

EMEA Region

Download Instructions (multilingual)

Mini Charger

ENHANCED COMMUNICATION

 Multiple colored LED lights indicate charge status









DONE



BAD (PULSING)

VERSATILE

• Charges 1 or 2 AA or AAA NiMH batteries



SAFETY TIMER

· Ensures charger is not active for extended periods of time



Energizer. NIMH CHARGER AA.AAA

Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Best used with *Energizer* NiMH batteries.

Product Detail:

Designation: Mini Charger

Model: CH2PC4

Color: Black

Charge Capability: "AA" (1) or (2)

"AAA" (1) or (2)

Note: Do not charge (1) "AA" and (1) "AAA"

at the same time. Please refer to the

instructions for orientation diagram.

Charging Times: Battery Capacity Estimated

(estimated) (NiMH) (mAh) (time) AA 1300-2000 7-10 hrs AA 2000-2400 10-12 hrs

AAA 500-800 5-8 hrs

Shutoff Mechanism: Timer (15 hours) Charging Current: "AA" 200mA "AAA" 100mA

Trickle Charge: None

Input Rating: 100-240VAC, 50/60Hz, 3W

Typical Weight: 65 grams

Dimensions (mm): 115 x 45 x 70 (L x W x H) Safety Features: Reverse Polarity Protection

Safety Timer to Prevent Overcharge

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

©2017 Energizer Brands, LLC

Contents herein do not constitute a warranty.