NiMH Battery Charger (CH1HR3)

European Region


FAST

 Charges NiMH batteries in about one hour



EASY TO USE

• Charger communicates charge status



VERSATILE

 Charges 1, 2, 3 or 4
 AA or AAA NiMH
 Batteries at a time



One Hour Battery Charger



Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Product Detail:

Designation: 1 Hour Charger

Color: Black

Charging Capability: 1 to 4 "AA" / 1 to 4 "AAA"

Charging Current: "AA" 2500mA

"AAA" 1000mA

Trickle Charge: "AA" 50mA

"AAA" 20mA

Charging Times: (estimated)

:	Battery	Capacity	Estimated
)	(NiMH)	(mAh)	(time)
	AA	1300	50 min
	AA	2000	54 min
	AA	2300	60 min
	AA	2400	60 min
	AAA	700	56 min
	AAA	800	60 min
	AAA	850	60 min

Shutoff Mechanism: Timer Control

Max Timer Control 80 mins
Charger Input: DC 11-16V
Weight (charger): 112 grams

Dimensions (mm): 115 x 75 x 32 (H x L x W) **Safety Features:** Reverse Polarity Protection

Safety Timer to Prevent Over Charge

Primary Battery Detection Temperature Control

Minus Delta Voltage Control (-dV)

NOTE: Do not attempt to charge non-rechargeable batteries not specified by Energizer

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

©Energizer

Contents herein do not constitute a warranty.