




客户料号:R620
客户确认:
产品图号:MWH08032BK

版次	详细描述	变更日期	变更者
A/1	XR-201更新字版	2015. 11. 16	陆剑



线材印字为凹印, 字轮编号: CY131
 印字内容: (UL) E218701 SPT-2 18AWGX2C 300V 105°C VW-1
 GUANGDONG XIONGRUN C(UL) TYPE SPT-2 2X0.824mm (18AWG)
 300V 105°C E218701 FT2



技术要求: requirement:

- 1: 耐压测试: 外高压4200V/S 内高压1500V/S 0.5-1.0mA
 Dielectric voltage: between jacket and conductors 4200V/S
 between conductors 1500V/S 0.5-1.0mA
- 2: 绝缘阻抗不小于100兆欧。
 Insulation resistance 100MΩ.
- 3: 100%导通OK.
 Continuity of lead 100% OK.
- 4: 符合ROHS指令.
 RoHS COMPLIANT
- 5: 180条一箱。
 180 pcs / carton

4	6mm鲨鱼齿端子, 18-22AWG, 黄铜本色 (6mm brass splice)	DWSYC00001T-0	2	EA
3	非极性插头non-polarized blade (XR-201) COLOR:black黑色, 30P PVC.	BC1030PBK0011	0.01382	Kg
2	平头非极性插片, 黄铜镀镍 (AC-009[non-polarized blade*2])	DA001002ST-1	2	EA
1	SPT-2 18AWGX2C, UL105° C COLOR:黑色black, 裁线长cut wire length:L=1990mm.	CUPT22018A00101	1	EA
NO.	DESCRIPTION	Xiongrun PN	QTY	unit



DESCRIPTION	AC POWER CABLE	DRAW NO.	XR-0672129	UNIT	M M
PARTS NO		SCALE	NONE	DATE	02/03/2011
APPROVED		CHECKED		DRAWING	