




客户料号:R621
产品图号:MWH08014BK

版次	详细描述	变更日期	变更者
A/1	增加扎线方式	2011/3/12	
A/2	更新XR-201插头	2015/7/15	
A/3	XR-503增加2.5A 250V~ 字样	2016/06/02	陆剑



线材印字为凹印, 字轮编号: CY131 wire marking:
(UL) E218701 SPT-2 18AWGX2C 300V 105°C VW-1
GUANGDONG XIONGRUN C(UL) TYPE SPT-2 2X0.824mm² (18AWG)
300V 105°C E218701 FT2



技术要求: requirement:
1: 耐压测试: 外高压4200V/S 内高压1500V/S 0.5-1.0mA
Dielectric voltage :between jacket and conductors 4200V/S
between conductors 1500V/S 0.5-1.0mA
2: 绝缘阻抗不小于100兆欧.
Insulation resistance 100MΩ.
3: 100%导通OK.
Continuity of lead 100% OK.
4: 符合ROHS指令.
RoHS COMPLIANT
5: 180条一箱.
180 pcs / carton

NO.	DESCRIPTION		Xiongrun PN	QTY	unit
7	UL两插内架, 白色 insert	2B0014-01	JB2012001-0	1	EA
6	八字尾内架, 黑色 inner body	2B0052-01	JB5032002-B	1	EA
5	Φ2.4母圆管端子, 18-22AWG, 磷铜本色 (98715) terminal*2	2A0241-01	DYM24001LL-0	2	EA
4	八字尾 (XR-503) 黑色 55P PVC connector (XR-503), black, PVC, 55P	3B0144-01	BC7055PBK0011	0.01	Kg
3	非极性插头non-polarized blade (XR-201) COLOR: black黑色, 30P PVC.	3B0105-01	BC7030PBK0011	0.01382	Kg
2	平头非极性插片, 黄铜镀镍 [non-polarized blade*2]	2A0003-01	DA001002ST-1	2	EA
1	SPT-2 18AWGX2C, UL105°C, COLOR: 黑色black, 裁线长cut wire length: L=1790mm.	U10611	CUPT22018A00101	1	EA

 **广东雄润电业有限公司**
GUANGDONG XIONGRUN ELECTRICAL CO., LTD

DESCRIPTION	AC POWER CABLE	DRAW NO.	XR-0672045	UNIT	M M
PARTS NO		SCALE	NONE	DATE	21/11/2008
APPROVED		CHECKED		DRAWING	