



# Art.Nr.53350.31

Singlemode LC/LC duplex adapter,  
Plastic housing blue, ceramic sleeve, White dust cap,



## Specification

Item	Parameter
Sleeve Material	Ceramic
Typical Insertion Loss, dB	0.1
Max Insertion Loss, dB	0.2
Durability(1000 Mating)	0.2dB Max.Increase
Operating Temperature, °C	-40 ~ +85
Storage Temperature, °C	-40 ~ +85

The performance of the adaptors has been carefully designed to meet the toughest Telcordia standards

### GR-326-CORE

**RoHS-Compliance of item and package  
Conformance according to IEC 61754-20**

in the tests of:

- OPTICAL CHARACTERISTICS
- VIBRATION TEST
- THERMAL CYCLING
- IMPACT RESISTANCE
- SALT SPRAY EROSION
- THERMAL AGING
- HUMIDITY RESISTANCE
- OTHERS

## Mechanical Diagram

