

Electronic housing - EMG 30-H 52MM GN - 2947909

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 30 mm

Key commercial data

package_quantity	5
GTIN	4017918083014

Technical data

General

Housing type	Upper part
Housing material	Polycarbonate fiber reinforced PC-F
Color	green

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
--	-------------------

Dimensions

Length	38 mm
Constructional height	52 mm
Width	30 mm

Technical data

Inflammability class according to UL 94	V0
Number of positions	10

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

Electronic housing - EMG 30-H 52MM GN - 2947909

classifications

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000886

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>