

Side element - UM 45-SEFE - 2907826

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Side element with foot, labeling with SS-ZB, mounted along the length of the DIN rail NS 35/7.5. Height: 36 mm, width: 10 mm, length: 45 mm.

Product Features

- UM ...-SES lateral element offers options for labeling with Phoenix Contact marking material
- Fast mounting
- Flexible size and shape
- Inexpensive as a result of reducing the number of separate housing parts
- High degree of mechanical stability by screwing the lateral elements to the profile
- The UMK-BF mounting flange enables modules to be mounted directly on the wall
- Cable fixing by means of UM ...-SEK lateral element (fixed using cable binders, not supplied as standard)

Key commercial data

package_quantity	10
GTIN	4017918147976

Technical data

General

Housing type	Side cover
Housing material	PA
Color	green

Technical data

Inflammability class according to UL 94	V0
--	----

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

Side element - UM 45-SEFE - 2907826

classifications

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000721


UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

UL Recognized /

Approval details



Drawings

Dimensioned drawing

