


MH-6 TYPE



ITEM NO.	D	d	H
MH14-6A	14±0.5	2.1±0.25	9.2±0.25
MH18-6A	17.5±0.5	2.0±0.25	9.0±0.25
MH18-6B	17.5±0.5	3.0±0.25	9.0±0.25
MH23-6A	22.8±0.5	2.0±0.25	11.2±0.35
MH23-6B	22.8±0.5	3.0±0.25	11.2±0.35
MH23-6C	22.8±0.5	3.6±0.25	11.2±0.35
MH23-6D	22.8±0.5	5.2±0.25	11.2±0.35
MH30-6A	30.4±1.0	3.6±0.25	14.4±0.35
MH30-6B	30.4±1.0	5.2±0.25	14.4±0.35
MH30-6C	30.4±1.0	7.0±0.25	14.4±0.35

		MATERIAL	ITEM NO.
		TPE	MH-6 TYPE
SCALE		FINISH	NAME Multi-Hole Seal (6 HOLES)
△ (. .)	TOLERANCE AS FIGURE	△ (. .) DATE	REVISIONS K001
			R.NO.

