

C315C104M5U5TA

aka C315C104M5U5TA

Capacitor, ceramic, 0.1 uF, +/-20% Tol, 50V, Z5U, Lead Spacing=0.1"



Dimensions (in)

Specifications

ID	Dimension	Tolerance	Manufacturer:	KEMET
L	0.15	max	Capacitance:	0.1 uF
H	0.21	max	Lead Spacing:	0.1"
T	0.1	max	Voltage:	50V
S	0.1	+/-0.03	Temperature Coefficient:	Z5U
LL	0.276	min	Tolerance:	+/-20%
F	0.02	+0.004/-0.001	Body Type:	Radial Conformal
K	0.02		Lead Type:	Standard Leads
			Lead Form:	Straight Leads
			Termination Type:	Tin
			Package Kind:	Bulk
			Package Type:	Bag
			Package Quantity:	500

Notes:

-Lead length shown is for parts supplied in bulk. See packaging specifications for lead lengths when not provided in bulk