


Capacitor, tantalum, 100 uF, 7343, +/-10% Tol, 16V@85C



## Dimensions (mm)

## Specifications

ID	Dimension	Tolerance	Manufacturer:	KEMET
L	7.3	+/-0.3	Capacitance:	100 uF
W	4.3	+/-0.3	Voltage DC @ 85C:	16V
H	2.8	+/-0.3	Voltage DC @ 105C:	13V
K	1.5	+/-0.2	Voltage DC @ 125C:	10V
F	2.4	+/-0.1	Tolerance:	+/-10%
S	1.3	+/-0.3	Application:	General Purpose
B	0.5	+/-0.15	Body Type:	Molded Chip
X	0.1	ref	Temperature Range:	-55/+125C
P	0.9	ref	ESR:	700 mOhm
R	1	ref	Footprint:	7343
T	0.13	ref	Termination:	Tin
A	3.8	ref	Leakage Current:	16 uA
G	3.5	ref	Dissipation Factor:	8%
E	3.5	ref	Ripple @ 25C:	0.463 A
			Ripple @ 85C:	0.417 A
			Ripple @ 125C:	0.185 A
			Package Kind:	T&R
			Package Quantity:	500