

# Crimping pliers - CRIMPFOX 25R - 1212039

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for ferrules as per DIN 46228 section 1+4, 10-25 mm<sup>2</sup>, insertion from the side, WM crimp

## Product Features

- Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25%



## Key commercial data

package_quantity	1
GTIN	4046356453905

## Technical data

### Dimensions

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm

### General

Compression	WM crimp
Type of contact	Ferrules
Name	Crimping position 1
Max. cross section	10 mm <sup>2</sup>
AWG max	8
Name	Crimping position 2
Max. cross section	16 mm <sup>2</sup>
AWG max	6
Name	Crimping position 3
Max. cross section	25 mm <sup>2</sup>
AWG max	4
Die station	Crimping position 4
Die station	Crimping position 5

# Crimping pliers - CRIMPFOX 25R - 1212039

## classifications

### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

## approvals

GOST /

### Approval details



## accessories

### Die

CRIMPFOX 25R/DIE - 1212040



## Mounting material

# Crimping pliers - CRIMPFOX 25R - 1212039

accessories

CRIMPFOX/ SPR-1 - 1212069



---

## Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>