

Replacement die - CRIMPFOX-M 25/DIE - 1212081

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Die, for Crimpfox-M, for ferrules 16 - 25 mm², packed in a serial storage box

Key commercial data

package_quantity	1
GTIN	4046356454513

Technical data

Dimensions

Length (b)	114 mm
Height	25.5 mm
Width (a)	75 mm

General

Color	black
Compression	Trapezoidal crimp
Type of contact	Ferrules
Name	Crimping position 1
Max. cross section	16 mm ²
AWG max	6
Name	Crimping position 2
Max. cross section	25 mm ²
AWG max	4

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

Replacement die - CRIMPFOX-M 25/DIE - 1212081

classifications

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>