

Electrical crimping tool - CF 1000-1,5 - 1208199

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Stripping and crimping machine, 100 - 240 V input voltage, for insulated ferrules with a cross-section range of 0.25 - 4.0 mm², in accordance with DIN 46228-4: 1990-09, incl. installation kits 0.5 - 1.5 mm² (8 mm sleeve length)

Product Features

- Quick change of cross section without the need for additional adjustments
- Suitable for bulk processing
- Up to 1200 conductors can be processed an hour
- Rugged design
- The pull-out forces meet the requirements of IEC/EN 60999 and IEC/EN 60947
- The stripping and crimping machine can be used to process loose ferrules with insulating collars according to DIN 46228-4
- Quantity counter
- The conductor is stripped in a single step and crimped with a ferrule to a high standard of quality

Key commercial data

package_quantity	1
GTIN	4046356011341

Technical data

Dimensions

Length (b)	490 mm
Height	390 mm
Width (a)	240 mm

General

Compression	trapezoidal
Air consumption per compression	1.2 l
Working cycle	1.5 s
Test standard	DIN 46228-4: 1990-09

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301

Electrical crimping tool - CF 1000-1,5 - 1208199

classifications

eCl@ss

eCl@ss 5.1	21040301
eCl@ss 6.0	17130101
eCl@ss 7.0	17130101
eCl@ss 8.0	17130101

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC002778

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



accessories

Conversion kit

CF 1000-TOOLKIT 0,34/ 6 - 1208212



Electrical crimping tool - CF 1000-1,5 - 1208199

accessories

CF 1000-TOOLKIT 0,34/ 8 - 1208225



CF 1000-TOOLKIT 2,5/ 8 - 1208241



CF 1000-TOOLKIT 4,0/10 - 1208270



Knife

CF 1000 EM - 1205215



CF 1000 EM4,0 - 1212663



Separation

Electrical crimping tool - CF 1000-1,5 - 1208199

accessories

CF 1000 SORT0,34 - 1206890



CF 1000 SORT1,5 - 1204326



CF 1000 SORT2,5 - 1206874



CF 1000 SORT4,0 - 1206887



CF 1000 VEP1,5 - 1206900



CF 1000 VEP2,5 - 1206926



Electrical crimping tool - CF 1000-1,5 - 1208199

accessories

CF 1000 VEP0,34 - 1206939



CF 1000 VEP4,0 - 1206942



Sleeve receiver

CF 1000 HWB1,5 - 1206955



CF 1000 HWB4,0 - 1206968



CF 1000 HWB0,34 - 1206971



Electrical crimping tool - CF 1000-1,5 - 1208199

accessories

CF 1000 HA0,5 - 1206984



CF 1000 HA0,75 - 1206997



CF 1000 HA1,0 - 1207006



CF 1000 HA1,5 - 1207019



CF 1000 HA2,5 - 1207022



CF 1000 HA0,34 - 1207035



Electrical crimping tool - CF 1000-1,5 - 1208199

accessories

CF 1000 HA4,0 - 1207048



CF 1000 HAS 6-0,34 - 1212678



CF 1000 HAS 8-0,34 - 1212679



CF 1000 HAS 6-1,5 - 1212680



CF 1000 HAS 8-2,5 - 1212681



Electrical crimping tool - CF 1000-1,5 - 1208199

accessories

CF 1000 HAS 10-2,5 - 1212682



CF 1000 HAS 10-4,0 - 1212683



Crimping machine

CF 1000 LZT1,5 - 1207051



CF 1000 LZT0,75 - 1207064



CF 1000 LZT2,5 - 1207077



Electrical crimping tool - CF 1000-1,5 - 1208199

accessories

CF 1000 LZT0,34 - 1207080



CF 1000 LZT4,0 - 1207093



CF 1000 ST 6-0,34 - 1212672



CF 1000 ST 8-0,34 - 1212673



CF 1000 ST 6-1,5 - 1212674



CF 1000 ST 8-2,5 - 1212675



Electrical crimping tool - CF 1000-1,5 - 1208199

accessories

CF 1000 ST 10-2,5 - 1212676



CF 1000 ST 10-4,0 - 1212677



CF 1000 ADW - 1212684

Die

CF 1000 PB 6-2,5 - 1207145



CF 1000 PB 8-2,5 - 1207158



Electrical crimping tool - CF 1000-1,5 - 1208199

accessories

CF 1000 PB 10-2,5 - 1207161



CF 1000 PB 6-0,34 - 1212666



CF 1000 PB 8-0,34 - 1212667



CF 1000 PB 10-4 - 1212668



Fuse

CF 1000 SICHERUNG - 1207190



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>