

# Tool - SF-BIT-SLS 0,9X6,5-50 - 1212606

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Screw bit, bladed, graded, E6.3-1/4" drive, for test socket screws, size: 0.9 x 6.5 x 50 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1173

The figure shows the SF-BIT-SLS 0,6x3,5 version

## Product Features

- Tools for SF-ASD 21 cordless screwdriver in various versions

## Key commercial data

|                         |               |
|-------------------------|---------------|
| <b>package_quantity</b> | 5             |
| <b>GTIN</b>             | 4046356590297 |

## Technical data

### Dimensions

|                        |        |
|------------------------|--------|
| <b>Blade thickness</b> | 0.9 mm |
| <b>Blade width</b>     | 6.5 mm |
| <b>Blade height</b>    | 50 mm  |

### General

|                      |                    |
|----------------------|--------------------|
| <b>Color</b>         | silver             |
| <b>Design</b>        | Bladed             |
| <b>Type</b>          | Stepped blade      |
| <b>Material</b>      | Alloyed tool steel |
| <b>Test standard</b> | DIN 3126           |

## classifications

### eCl@ss

|                   |          |
|-------------------|----------|
| <b>eCl@ss 4.0</b> | 21040402 |
| <b>eCl@ss 4.1</b> | 21040402 |
| <b>eCl@ss 5.0</b> | 21040402 |
| <b>eCl@ss 5.1</b> | 21040402 |
| <b>eCl@ss 6.0</b> | 21040290 |
| <b>eCl@ss 7.0</b> | 21040290 |
| <b>eCl@ss 8.0</b> | 21040290 |

# Tool - SF-BIT-SLS 0,9X6,5-50 - 1212606

## classifications

### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 4.0</b> | EC002115 |
| <b>ETIM 5.0</b> | EC002115 |

### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 27111701 |
| <b>UNSPSC 7.0901</b> | 27111701 |
| <b>UNSPSC 11</b>     | 27111701 |
| <b>UNSPSC 12.01</b>  | 27111701 |
| <b>UNSPSC 13.2</b>   | 27111701 |

## approvals

---

GOST /

---

### Approval details



## Drawings