

Crimping pliers - CRIMPFOX-RCI 2,5 - 1212053

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for insulated cable lugs, 0.75 - 2.5 mm² (red, blue), oval crimp

Product Features

- ✓ The color-coded dies clearly indicate the cross section
- ✓ Unlockable pressure lock
- ✓ They unlock as soon as the required crimping pressure is reached, therefore ensuring sufficient pressure is applied



Key commercial data

package_quantity	1
GTIN	4046356453820

Technical data

Dimensions

Length (b)	198 mm
Height	59 mm
Width (a)	18 mm

General

Compression	Oval crimp
Type of contact	Insulated cable lugs
Name	Crimping position 1
Min. cross section	0.75 mm ²
Max. cross section	1.5 mm ²
AWG min	20
AWG max	16
Name	Crimping position 2
Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
AWG min	16
AWG max	14
Name	Crimping position 3

Crimping pliers - CRIMPFOX-RCI 2,5 - 1212053

Technical data

General

Die station	Crimping position 4
Die station	Crimping position 5

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details

GOST 

accessories

Die

Crimping pliers - CRIMPFOX-RCI 2,5 - 1212053

accessories

CRIMPFOX-RCI 2,5/DIE - 1212054



Mounting material

CRIMPFOX/ SPR-3 - 1212036



Drawings

Product drawing

