

Pneumatic crimping tool - ZAP 25 - 1203110


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Pneumatic crimping pliers, for ferrules in accordance with DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09, for conductor cross section 0.25 - 2.5 mm²

Product Features

- These crimping pliers are pneumatic tools for ferrules with a cross section range of 0.25 to 10 mm²
- The ZAP 25 has a Duo-Press die, allowing both front and lateral conductor entry



Key commercial data

package_quantity	1
GTIN	4017918018085

Technical data

Dimensions

Length (b)	190 mm
------------	--------

General

Compression	trapezoidal
Min. AWG, flexible, multi-strand	14
AWG max., flexible, multi-strand	24
Pressure range	4 bar ... 6 bar
Air consumption per compression	0.2 l

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	17130101
eCl@ss 7.0	17130101
eCl@ss 8.0	17130101

Pneumatic crimping tool - ZAP 25 - 1203110

classifications

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC002778

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details

GOST

Drawings