

## Diagonal cutter - MICROFOX-S ESD - 1212480

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



ESD electronic diagonal cutter, round head, without chamfer, with opening spring, non-reflective coating and phosphate-treated, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1 mm diameter

### Product Features

- ✓ Ergonomically designed two-component handles for fatigue-proof and non-slip use
- ✓ Opening spring for uniform, smooth opening
- ✓ Made from special high-grade tool steel
- ✓ Screwed precision-joint for permanent stability and optimum results
- ✓ Mirror-polished and phosphate-treated metal surfaces for optimum rust protection and no glare when working
- ✓ The special conductive plastic handles ensure slow and safe removal of electrostatic energy according to standards and directives such as DIN EN 61340-5



### Key commercial data

package_quantity	1
GTIN	4046356527125

### Technical data

#### Dimensions

Length (b)	110 mm
------------	--------

### classifications

#### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043706
eCl@ss 7.0	21043706
eCl@ss 8.0	21043706

#### ETIM

ETIM 2.0	EC001186
----------	----------

# Diagonal cutter - MICROFOX-S ESD - 1212480

## classifications

### ETIM

<b>ETIM 3.0</b>	EC001186
<b>ETIM 4.0</b>	EC000165
<b>ETIM 5.0</b>	EC000165

### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39121410


## approvals

---

GOST /

---

### Approval details



## Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>