

Crimping pliers - CRIMPFOX 10S - 1212045

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for ferrules according to DIN 46228, 0.14 - 10 mm², pressure lock can be unlocked, lateral entry

Product Features

- These compact crimping pliers have been designed to reduce effort when working
- The way in which the handles and the die are arranged means that the ferrules can be fitted however the tool is held



Key commercial data

package_quantity	1
GTIN	4046356455732

Technical data

Dimensions

Length (b)	175 mm
------------	--------

General

Compression	Square crimp
Type of contact	Ferrules

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186

Crimping pliers - CRIMPFOX 10S - 1212045

classifications

ETIM

ETIM 4.0	EC001186
ETIM 5.0	EC000168


UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



accessories

Mounting material

CRIMPFOX/SPR-2 - 1212047



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>