

Replacement die - CRIMPFOX-M CX-2/DIE - 1212088

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Die, for Crimpfox-M, for coaxial connectors (BNC/TNC) RG 58/ 59/ 62/ 71, packed in a serial storage box

Key commercial data

| | |
|-------------------------|---------------|
| package_quantity | 1 |
| GTIN | 4046356454483 |

Technical data

Dimensions

| | |
|-------------------|---------|
| Length (b) | 114 mm |
| Height | 25.5 mm |
| Width (a) | 75 mm |

General

| | |
|---------------------------|----------------------|
| Color | black |
| Compression | HEX crimp |
| Type of contact | Coaxial connectors |
| Max. cross section | 1.69 mm ² |
| Min. cross section | 5.41 mm ² |
| Max. cross section | 6.48 mm ² |

classifications

eCl@ss

| | |
|-------------------|----------|
| eCl@ss 4.0 | 21040301 |
| eCl@ss 4.1 | 21040301 |
| eCl@ss 5.0 | 21040301 |
| eCl@ss 5.1 | 21040301 |
| eCl@ss 6.0 | 21043811 |
| eCl@ss 7.0 | 21043811 |
| eCl@ss 8.0 | 21043811 |

ETIM

| | |
|-----------------|----------|
| ETIM 2.0 | EC001186 |
| ETIM 3.0 | EC001186 |

Replacement die - CRIMPFOX-M CX-2/DIE - 1212088

classifications

ETIM

| | |
|-----------------|----------|
| ETIM 4.0 | EC001282 |
| ETIM 5.0 | EC001282 |


UNSPSC

| | |
|----------------------|----------|
| UNSPSC 6.01 | 27112118 |
| UNSPSC 7.0901 | 27111518 |
| UNSPSC 11 | 23171604 |
| UNSPSC 12.01 | 27111518 |
| UNSPSC 13.2 | 27111518 |

approvals

GOST /

Approval details



Drawings