

Crimping pliers - CRIMPFOX-SC 6 - 1212050

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for non-insulated slip-on sleeves 2.8 and 4.8 mm, 0.5 - 6 mm², B crimp

Product Features

- ✓ Consistently high crimping quality
- ✓ Marked die stations for precise processing of corresponding cross sections
- ✓ Unlockable pressure lock



Key commercial data

package_quantity	1
GTIN	4046356453950

Technical data

Dimensions

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm

General

Color	black
Compression	B crimp
Type of contact	Slip-on sleeve
Name	Crimping position 1
Min. cross section	0.5 mm ²
Max. cross section	1.5 mm ²
AWG min	22
AWG max	16
Name	Crimping position 2
Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
AWG min	16
AWG max	14

Crimping pliers - CRIMPFOX-SC 6 - 1212050

Technical data

General

Name	Crimping position 3
Min. cross section	2.5 mm ²
Max. cross section	6 mm ²
AWG min	14
AWG max	10
Die station	Crimping position 4
Die station	Crimping position 5

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details

GOST 
--

Crimping pliers - CRIMPFOX-SC 6 - 1212050

accessories

Die

CRIMPFOX-SC 6/DIE - 1212051



Mounting material

CRIMPFOX/ SPR-1 - 1212069



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>