

Crimping pliers - CRIMPFOX 6S-F - 1212043

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for ferrules as per DIN 46228 section 1+4, 0.5 - 6 mm², insertion from the front, square crimp

Product Features

- Comprehensive range of crimping pliers
- All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross sections
- Consistently high crimping quality
- Marked die stations for precise processing of corresponding cross sections
- Unlockable pressure lock



Key commercial data

package_quantity	1
GTIN	4046356453875

Technical data

Dimensions

Length (b)	198 mm
Height	59 mm
Width (a)	18 mm

General

Color	black
Compression	Square crimp
Type of contact	Ferrules
Name	Crimping position 1
Min. cross section	0.5 mm ²
Max. cross section	6 mm ²
AWG min	20
AWG max	10
Name	Crimping position 2
Name	Crimping position 3
Die station	Crimping position 4

Crimping pliers - CRIMPFOX 6S-F - 1212043

Technical data

General

Die station	Crimping position 5
-------------	---------------------

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



accessories

Mounting material

Crimping pliers - CRIMPFOX 6S-F - 1212043

accessories

CRIMPFOX/ SPR-3 - 1212036



accessories

CRIMPFOX 6S-F/DIE - 1212285

Drawings

Product drawing



