

Screwdriver - SF-SL 0,5X3,0-80 - 1212548

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Screwdriver, slot-headed, size: 0.5 x 3.0 x 80 mm, 2-component grip, with non-slip grip

The figure shows the SZF 1 version

Product Features

- The tools feature ergonomic two-component safety handles
- Large contact surface of blades inside screw head
- Individually tested safety screwdrivers according to DIN EN 60900 (VDE 0682-201)
- For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC

Key commercial data

package_quantity	10
GTIN	4046356589833

Technical data

Dimensions

Length (b)	161 mm
Width (a)	26 mm
Blade thickness	0.5 mm
Blade width	3 mm
Blade height	80 mm

General

Design	Bladed
Type	Straight
Material	Alloyed tool steel
Test standard	DIN/ISO 2380-1

classifications

eCl@ss

eCl@ss 4.0	21040401
eCl@ss 4.1	21040401
eCl@ss 5.0	21040401
eCl@ss 5.1	21040401

Screwdriver - SF-SL 0,5X3,0-80 - 1212548

classifications

eCl@ss

eCl@ss 6.0	21040401
eCl@ss 7.0	21040409
eCl@ss 8.0	21040409

ETIM

ETIM 4.0	EC000158
ETIM 5.0	EC000158


UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



Drawings

Screwdriver - SF-SL 0,5X3,0-80 - 1212548

Pictogram

