

Crimping pliers - CRIMPFOX-RCT 25-1 - 1212066

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for non-insulated conduit lugs, 10 - 25 mm², HEX crimp

Product Features

- CRIMPFOX-RC 10 and ...RCT 25-1 complete the range of crimping pliers for uninsulated cable lugs and insulated tube lugs
- All pliers of this type reduce the amount of force required during crimping by 25%



Key commercial data

package_quantity	1
GTIN	4046356454063

Technical data

Dimensions

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm

General

Color	black
Compression	HEX crimp
Type of contact	CU conduit lugs
Name	Crimping position 1
Max. cross section	10 mm ²
AWG max	8
Outside diameter	7.00 mm
Internal diameter	4.50 mm
Name	Crimping position 2
Max. cross section	16 mm ²
AWG max	6
Outside diameter	8.50 mm
Internal diameter	5.50 mm
Name	Crimping position 3
Max. cross section	25 mm ²

Crimping pliers - CRIMPFOX-RCT 25-1 - 1212066

Technical data

General

AWG max	4
Outside diameter	10.00 mm
Internal diameter	7.00 mm

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



accessories

Die

Crimping pliers - CRIMPFOX-RCT 25-1 - 1212066

accessories

CRIMPFOX-RCT 25-1/DIE - 1212300



Mounting material

CRIMPFOX/ SPR-1 - 1212069



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>