

Crimping pliers - CRIMPFOX-RC 2,5 - 1212063

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for uninsulated cable lugs, 0.34 - 2.5 mm², indent crimp

Product Features

- Compact and lightweight design
- Ergonomically designed handles ensure an optimum grip and help avoid fatigue when working
- Consistently high crimping quality
- For processing uninsulated cable lugs
- Unlockable pressure lock
- Lateral conductor entry
- Marked die stations for precise processing of corresponding cross sections



Key commercial data

package_quantity	1
GTIN	4046356453844

Technical data

Dimensions

Length (b)	198 mm
Height	59 mm
Width (a)	18 mm

General

Compression	Indent crimp
Type of contact	Non-insulated cable lugs
Name	Crimping position 1
Min. cross section	0.34 mm ²
Max. cross section	0.75 mm ²
AWG min	22
AWG max	20
Name	Crimping position 2
Min. cross section	0.75 mm ²
Max. cross section	1.5 mm ²

Crimping pliers - CRIMPFOX-RC 2,5 - 1212063

Technical data

General

AWG min	14
AWG max	16
Name	Crimping position 3
Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
AWG min	16
AWG max	14
Die station	Crimping position 4
Die station	Crimping position 5

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



Crimping pliers - CRIMPFOX-RC 2,5 - 1212063

accessories

Die

CRIMPFOX-RC 2,5/DIE - 1212064



Mounting material

CRIMPFOX/ SPR-3 - 1212036



Drawings

Product drawing

