

Crimping pliers - CRIMPFOX-RCI 6 - 1212057

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for insulated cable lugs, 0.75 - 6.0 mm² (red, blue, yellow), oval crimp, symmetrical

Product Features

- CRIMPFOX-RCI 6 /... represent the top end of the range for cable lug crimping pliers
- Precision-manufactured dies ensure consistently high levels of quality during contact processing



Key commercial data

package_quantity	1
GTIN	4046356453929

Technical data

Dimensions

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm

General

Color	black
Compression	Oval crimp
Type of contact	Insulated cable lugs
Name	Crimping position 1
Min. cross section	0.75 mm ²
Max. cross section	1.5 mm ²
AWG min	20
AWG max	16
Name	Crimping position 2
Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
AWG min	16
AWG max	14
Name	Crimping position 3

Crimping pliers - CRIMPFOX-RCI 6 - 1212057

Technical data

General

Min. cross section	2.5 mm ²
Max. cross section	6 mm ²
AWG min	14
AWG max	10
Die station	Crimping position 4
Die station	Crimping position 5

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



Crimping pliers - CRIMPFOX-RCI 6 - 1212057

accessories

Die

CRIMPFOX-RCI 6/DIE - 1212058



Mounting material

CRIMPFOX/ SPR-1 - 1212069



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>