

## Replacement die - CF 500/DIE AI 6 - 1212238

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Die for CF 500 crimping machine, for ferrules (A... and AI...) 0.08 - 6 mm<sup>2</sup>

### Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356449830

### Technical data

#### General

<b>Compression</b>	Trapezoidal crimp
<b>Min. cross section</b>	0.08 mm <sup>2</sup>
<b>Max. cross section</b>	6 mm <sup>2</sup>

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	21043074
<b>eCl@ss 4.1</b>	21043074
<b>eCl@ss 5.0</b>	21043290
<b>eCl@ss 5.1</b>	21059090
<b>eCl@ss 6.0</b>	17130101
<b>eCl@ss 7.0</b>	17130101
<b>eCl@ss 8.0</b>	17130101

#### ETIM

<b>ETIM 3.0</b>	EC001186
<b>ETIM 4.0</b>	EC001282
<b>ETIM 5.0</b>	EC001282

#### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	27111518
<b>UNSPSC 13.2</b>	39121410

## Replacement die - CF 500/DIE AI 6 - 1212238

approvals

---

GOST /

---

Approval details



Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>