

Crimping pliers - CRIMPFOX 50R - 1212041

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for ferrules as per DIN 46228 section 1+4, 35 - 50 mm², insertion from the side, WM crimp

Product Features

- Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25%



Key commercial data

package_quantity	1
GTIN	4046356453912

Technical data

Dimensions

Length (b)	256 mm
Height	68 mm
Width (a)	25 mm

General

Compression	WM crimp
Type of contact	Ferrules
Name	Crimping position 1
Max. cross section	35 mm ²
AWG max	2
Name	Crimping position 2
Max. cross section	50 mm ²
AWG max	1
Name	Crimping position 3
Die station	Crimping position 4
Die station	Crimping position 5

classifications

eCl@ss

Crimping pliers - CRIMPFOX 50R - 1212041

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



accessories

Die

CRIMPFOX 50R/DIE - 1212042



Mounting material

Crimping pliers - CRIMPFOX 50R - 1212041

accessories

CRIMPFOX/ SPR-1 - 1212069



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>