

Replacement die - CRIMPFOX-M RCI 6/DIE - 1212073

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Die, for Crimpfox-M, for insulated cable lugs 0.1 - 0.4 mm² and 4 - 6 mm² (light green, yellow), packed in a serial storage box

Key commercial data

package_quantity	1
GTIN	4046356452526

Technical data

Dimensions

Length (b)	114 mm
Height	25.5 mm
Width (a)	75 mm

General

Color	black
Compression	Oval crimp
Type of contact	Insulated cable lugs
Name	Crimping position 1
Min. cross section	0.1 mm ²
Max. cross section	0.4 mm ²
AWG min	26
AWG max	22
Name	Crimping position 2
Min. cross section	4 mm ²
Max. cross section	6 mm ²
AWG min	12
AWG max	10

classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301

Replacement die - CRIMPFOX-M RCI 6/DIE - 1212073

classifications

eCl@ss

eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282


UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



Drawings